



Price\* : 129.35 GBP



## Main

|                    |                                                               |
|--------------------|---------------------------------------------------------------|
| Range              | Thalassa                                                      |
| Product name       | Thalassa PLM                                                  |
| Device short name  | PLM                                                           |
| Enclosure type     | Multi-purpose                                                 |
| Category           | Compact enclosure                                             |
| Nominal height     | 530 mm                                                        |
| Nominal width      | 430 mm                                                        |
| Nominal depth      | 200 mm                                                        |
| Enclosure mounting | Wall mounted                                                  |
| Device composition | Lock 2<br>Door 1<br>Body 1<br>Mounting plate 1                |
| Body type          | One piece moulded with notches in the rear<br>Built-in canopy |
| Door type          | Plain                                                         |
| Lock type          | 3 mm double-bar lock                                          |

## Complementary

|                             |                                                               |
|-----------------------------|---------------------------------------------------------------|
| Number of locks             | 2                                                             |
| Mounting plate description  | Plain steel                                                   |
| Accessibility for operation | Front                                                         |
| Removable parts             | Door by hinges<br>Mounting plate by fixing element            |
| Material                    | Polyester reinforced with fibreglass                          |
| Colour                      | Grey RAL 7035                                                 |
| Standards                   | IEC 62208<br>NEMA classification 13<br>NEMA classification 4X |

|                        |    |
|------------------------|----|
| Product certifications | UL |
|------------------------|----|

## Environment

|                                     |                  |
|-------------------------------------|------------------|
| IP degree of protection             | IP66 IEC 60529   |
| IK degree of protection             | IK10 IEC 62262   |
| Fire resistance                     | 960 °C IEC 62208 |
| Ambient air temperature for storage | -35...90 °C      |

## Offer Sustainability

|                                  |                                                                                                                                       |
|----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                                                 |
| RoHS (date code: YYWW)           | Compliant - since 1511 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available                                                                                                                             |
| Product end of life instructions | Need no specific recycling operations                                                                                                 |