



Price* : 136.43 GBP



Main

Range	Spacial
Product or component type	Flexicable gland plate
Accessory / separate part category	Cable management accessory
Application	Multi-purpose
Range compatibility	Spacial S3D
Mounting location	Enclosure bottom
Cable gland type	Pierceable by screwdriver
Type of gland plate	Membrane
Cable outer diameter	10...26 mm
Cable entry	Without
Device composition	Membrane 1 plate
Quantity per set	Set of 1
Material	HCE (heat curable elastomer) for membrane Steel for plate

Complementary

Colour	Plate : grey RAL 7035
Surface finish	Epoxy-polyester powder
Height	30 mm
Width	Real : 510 mm 495 mm
Depth	220 mm
Product weight	1.258 kg
Thickness	1.5 mm
Number of cut-out	Undrilled
Cut-out dimensions	428 x 63 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available  Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------