




1 2 3 4 5 6 7 8

A






PCB LAYOUT TOP VIEW


B

C

D



PLUG SPEC




CIRCUIT DIAGRAM

E

F

G

H



|     |           |     |                         |           |
|-----|-----------|-----|-------------------------|-----------|
| ④   | HOUSING   | 1   | PBT Black)              |           |
| ③   | TERMINAL  | 1   | BRASS t=0.30            | Ag-Plated |
| ②   | TERMINAL  | 1   | PHOSPHOR BRONZE t=0.30  | Ag-Plated |
| ①   | TERMINAL  | 1   | H62 φ=0.65              | Ag-Plated |
| No. | PART NAME | QTY | MATERIAL (THICK, COLOR) | REMARK    |

**RoHS**  
**Compliant**

APPD.  
核准  
DWG.  
製圖  
Hedy  
DATE 制表日  
2019/02/20

SCALE  
比例  
參考  
UNIT  
單位  
MM  
PAGE  
張數  
1 / 1

TOLERANCE  
容許公差  
.0 ±  
.00 ±  
ANG.  
ANG.  
SIZE.  
紙張尺寸  
A 4  
REV.  
版次  
A  
PART NAME 品名  
DC POWER JACK RIGHT ANGLE TYPE  
PINφ0.7mm NORMAL CLOSE TYPE  
WITH LOCATING PEG WITHOUT SHIELDED  
SILVER PLATING BLACK COLOR ROHS  
PART NO.  
料號  
PC-GK0.65

|                          |       |       |       |         |
|--------------------------|-------|-------|-------|---------|
| UNSPECIFIED<br>TOLERANCE | ≤4    | 4-16  | ≥16   | ANGULAR |
|                          | ±0.15 | ±0.20 | ±0.30 | ±5°     |

1 2 3 4 5 6 7 8