



Electric Components > Products > Circular Connectors > Circular Connectors Power M 23 >
M 23 Power Straight Connector, Female Thread > [Straight Connector, for cables 7-12 mm 7.550.500.000](#)

Straight Connector, for cables 7-12 mm 7.550.500.000

cable diameter	7 – 12 mm
Housing material	Copper-Zinc alloy, Die Cast
Operating-Temperature	-40 – 125 °C
Protection category	IP67/ IP69K plugged
Seals / O-Rings	Buna-N standard
Surface material	Nickel

Additional information

- // [Assembly instruction Female Straight connector](#)
- // [Female Straight connector 5+3+PE](#)

