








T:1.6 Dimensions of PC board holes
Tolerance : ± 0.05 (Printed-top view)

PIN	SCHEMATIC
$\phi 2.0$	

UNLESS OTHERWISE SPECIFIED, TOLERANCE ON DECIMAL: ± 0.3

5	HOUSING	1	PBT 4815	UL-94V0(BLACK)
4	COVER	1	PBT 4815	UL-94V0(BLACK)
3	PIN	1	H59(COPPER ALLOY)	Ni PLATED
2	TERMINAL	1	C5191 t=0.25	Sn PLATED
1	TERMINAL	1	C2680 t=0.35	Sn PLATED

RoHS
Compliant

HSM 玄茂科技股份有限公司
HSUAN MAO TECHNOLOGY CO., LTD.

APPD. 核准		TOLERANCE 容許公差	PART NAME 品名
DWG. 製圖	SCALE 比例	.0 ± .00 ± ANG. ±	DC POWER JACK $\phi 2.0$ mm RIGHT ANGLE TYPE 2PIN NICKEL PLATED BLACK INSULATOR ROHS
DATE 制表日	UNIT 單位	SIZE. 紙張尺寸	PART NO.
2016/11/30	M M	A 4	料號 C9743-CCRN001R
	PAGE 張數	REV. 版次	
	1 / 1	A	