




6	HOUSING	1	PA10T	UL-94V0(BLACK)
5	GROUND SHIELD	1	C5191 t=0.30	Ni PLATED
4	SHIELD PLATE	1	SUS301 t=0.10	
3	PEG	1	C2680 t=0.40	
2	TIP SPRING	1	C5191 t=0.30	Ag PLATED
1	CENTER PIN	1	ZINC ALLOY	Ni PLATED
LTR	PART NAME	QTY	MATERIAL	REMARK

APPD. 核准	SCALE 比例	TOLERANCE 容許公差	PART NAME 品名
DWG. 製圖	參考	0.00 ± 0.30	DC POWER JACK PINφ2.0mmNORMAL OPEN TYPE
DATE 制表日	UNIT 單位	ANG. ± 3°	NICKEL PLATING W/ LOCATING PEG
2018/12/18	M M	SIZE. 紙張尺寸	BLACK COLOR ROHS
	PAGE 張數	REV. 版次	PART NO.
	1 OF 1	A	料號 C9750-CPNB0000R