

**A-series
AEP 2C 10/16 BL**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	AEP 2C 10/16 BL
Order No.	2490390000
Version	A-series, End plate
GTIN (EAN)	4050118500837
Qty.	20 pc(s).

A-series
AEP 2C 10/16 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	2.1 mm	Width (inches)	0.083 inch
Height	78.83 mm	Height (inches)	3.104 inch
Depth	44.5 mm	Depth (inches)	1.752 inch
Net weight	3.494 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	Wemid	Colour	blue
UL 94 flammability rating	V-0		

Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
eClass 9.1	27-14-11-33	eClass 10.0	27-14-11-33

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks