

**A-series  
APP 3**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image****Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | APP 3                      |
| Order No.  | <a href="#">2489100000</a> |
| Version    | A-series, Separation plate |
| GTIN (EAN) | 4050118499315              |
| Qty.       | 50 pc(s).                  |

**A-series**  
**APP 3**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Width      | 2.5 mm   | Width (inches)  | 0.098 inch |
| Height     | 104.2 mm | Height (inches) | 4.102 inch |
| Depth      | 45.15 mm | Depth (inches)  | 1.778 inch |
| Net weight | 5.703 g  |                 |            |

**Temperatures**

|                                  |               |                                  |        |
|----------------------------------|---------------|----------------------------------|--------|
| Storage temperature, max.        | 40 °C         | Storage temperature, min.        | 10 °C  |
| Storage temperature              | 10 °C...40 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C        |                                  |        |

**Material data**

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

**Classifications**

|             |             |            |             |
|-------------|-------------|------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0   | EC000886    |
| eClass 9.0  | 27-14-11-92 | eClass 9.1 | 27-14-11-33 |
| eClass 10.0 | 27-14-11-92 |            |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |                                                                                                                             |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Engineering Data   | <a href="#">EPLAN</a>                                                                                                       |
| Engineering Data   | <a href="#">STEP</a>                                                                                                        |
| User Documentation | <a href="#">Additional Note DE</a><br><a href="#">Additional Note EN</a><br><a href="#">StorageConditionsTerminalBlocks</a> |

### A-series APP 3

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

