

**A-series, W-Series
ZQV 1.5N/5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	ZQV 1.5N/5
Order No.	1985500000
GTIN (EAN)	4050118369991
Qty.	20 pc(s).

**A-series, W-Series
ZQV 1.5N/5**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	16 mm	Width (inches)	0.63 inch
Height	21.9 mm	Height (inches)	0.862 inch
Depth	2.8 mm	Depth (inches)	0.11 inch
Net weight	1.537 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
--------------------------	-----	----------------	---------

Dimensions

Pitch in mm (P)	3.5 mm
-----------------	--------

Rating data

Rated current	17.5 A
---------------	--------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40		

Approvals

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	2434520000_BED-ANL.ZQV_A_REIHE.pdf StorageConditionsTerminalBlocks