

A-series
ZQV 2.5N/10 RD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	ZQV 2.5N/ 10 RD
Order No.	2108910000
GTIN (EAN)	4050118486018
Qty.	20 pc(s).

A-series
ZQV 2.5N/10 RD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	48.7 mm	Width (inches)	1.917 inch
Height	24.7 mm	Height (inches)	0.972 inch
Depth	2.8 mm	Depth (inches)	0.11 inch
Net weight	5.83 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Material	Wemid	Colour	red
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
Type of mounting	Direct mounting		

Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

Rating data

Rated current	24 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	2434520000_BED-ANL.ZQV_A_REIHE.pdf StorageConditionsTerminalBlocks