

REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT

Technical characteristics:

Specifications

DIN EN 60 664-1

DIN EN 61 984

Inserts

01. Number of contacts :10+PE

02. Rated Current :16A

03. Rated Voltage :500V

04. Pollution degree :3

05. Rated impulse voltage :6kv¹⁰06. Insulation resistance : $\geq 10\Omega$

07. Material:Polycarbonate

08. Rated voltage acc. to UL/CSA:600V

09. Limiting temperatures : $-40^{\circ}\text{C}\sim+125^{\circ}\text{C}$

10. Flammability acc. to UL94:V0

11. Mechanical working life

(mating cycles) : ≥ 500

Contacts

01. Material:Copper alloy

02. Surface:hard-silver plated

03. Contact resistance : $\leq 1\text{m}\Omega$



04. Terminal :Crimp terminal

05. Wire gauge :0.14-4.0mm² (AWG 26-12)

06. Stripping length :7.5mm

07. Rohs Compliance

Note:Crimp contact pins should
order separately



DETACHED LISTS	PART NO:	NINGBO DEGSON ELECTRICAL CO., LTD		
	APPD:	NAME:		
	CHKD:	DEE-010-MC		
	DRFT:	TITLE: CUSTOMER DRAWING		
THIRD ANGLE PROJECTION		DRAWING NO:	DEE-010-MC-E01	REV
		MM	DO NOT SCALE DRAWING	SHEET
		(INCH)	SCALE	1:1
		2	1	