

H

H

REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT

DATE

G

G

Technical characteristics:

Specifications

DIN EN 60 664-1

DIN EN 61 984

F

F

Inserts

01. Number of contacts :46+PE

02. Rated Current :16A

03. Rated Voltage :500V

04. Pollution degree :3

05. Rated impulse voltage :6kv₁₀

06. Insulation resistance :≥10Ω

07. Material:Polycarbonate

08. Rated voltage acc.to UL/CSA:600V

09. Limiting temperatures : -40℃~+125℃

10. Flammability acc.to UL94:V0

11. Mechanical working life

(mating cycles) :≥500

D

D

Contacts

01. Material:Copper alloy

02. Surface:hard-silver plated

03. Contact resistance :≤1mΩ

04. Terminal :Crimp terminal

05. Wire gauge :0.14-4.0mm² (AWG 26-12)

06. Stripping length :7.5mm

07. Rohs Compliance



Note:Crimp contact pins should
order separately

C

C

B

B



A

A

PART NO: /		NINGBO DEGSON ELECTRICAL CO., LTD	
APPD: 1452016.01.08		NAME: DEE-046-MC	
CHKD: 1452016.02.18		TITLE: CUSTOMER DRAWING	
DRFT: Mr. Yang 2016.09.25		REV DO-1	
THIRD ANGLE PROJECTION		SHEET 1/1	
DO NOT SCALE		DRAWING SCALE 1:1	