




REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT
1			

TYPE	Thread		Selection
	D1	D2	
D16A-SF-1L-M20	M20	—	
D16A-SF-1L-2M20	M20	M20	
D16A-SF-1L-M25	M25	—	
D16A-SF-1L-2M25	M25	M25	
D16A-SF-1L-PG16	PG16	—	
D16A-SF-1L-2PG16	PG16	PG16	
D16A-SF-1L-PG21	PG21	—	



Housings Feature

01. Material: Aluminium die-cast
02. Surface: Powder-coated
03. Color: grey (RAL 7037)
04. Material: Metal (Lever)
05. Limiting temperatures: -40 °C ~ +125 °C
06. Flammability acc to UL94: V0
07. Degree of protection acc. to EN60529 for coupled connector: IP65
08. Rohs Compliance

DETACHED LISTS	PART NO.:	DEGSON® 宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD
	APPD: HJS 2016.8.4	NAME: D16A-SF-1L-M/PG
	CHKD: CHK 2016.9.1	TITLE: CUSTOMER DRAWING
	DRFT: Mr. yang 2016.08.15	REV: DO-1
DRAWING NO.:		SHEET 1/1
THIRD ANGLE PROJECTION		SCALE 1:1