




| TYPE             | Thread(D1) | Selection |
|------------------|------------|-----------|
| D6B-SE-2g-M20    | M20        |           |
| D6B-SE-2g-M25    | M25        |           |
| D6B-SE-2g-PG13.5 | PG13.5     |           |
| D6B-SE-2g-PG16   | PG16       |           |

| REVISION RECORD |     |             |      |
|-----------------|-----|-------------|------|
| REV             | ECN | DESCRIPTION | DRFT |
|                 |     |             |      |
|                 |     |             |      |



### Hoods Feature

- 1.Material: aluminium die-cast
- 2.Surface: Powder-coated
- 3.Color: grey (RAL 7037)
- 4.Limiting temperatures:  $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$
- 5.Flammability acc to UL94: V0
- 6.Degree of protection acc.to EN60529 for coupled connector :IP65
- 7:Rohs compliance

|                          |                         |                                   |         |
|--------------------------|-------------------------|-----------------------------------|---------|
| PART NO.: /              |                         | NINGBO DEGSON ELECTRICAL CO., LTD |         |
| APPD: PJS 2017.7.1       | NAME:                   | D6B-SE-2g-M/PG                    |         |
| CHKD: CHK 2017.7.1       | TITLE: CUSTOMER DRAWING | REV                               | DO-1    |
| DRFT: Mr.yang 2017/06/28 | DRAWING NO:             | SHEET                             | 1/1     |
| THIRD ANGLE PROJECTION   |                         | DO NOT SCALE                      | DRAWING |
|                          |                         | SCALE                             | 1:1     |