




TYPE	Thread(D1) Selection
D10B-SE-4g-M20	M20
D10B-SE-4g-M25	M25
D10B-SE-4g-PG16	PG16

REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT



Hoods Feature

- 1.Material: aluminium die-cast
- 2.Surface:Powder-coated
- 3.Color:grey(RAL 7037)
- 4.Limiting temperatures:-40°C ~ +125°C
- 5.Flammability acc to UL94:V0
- 6.Degree of protection acc.to EN60529 for coupled connector :IP65
- 7.Rohs compliance

PART NO: /		NINGBO DEGSON ELECTRICAL CO., LTD	
APPD: H/S 2017.7.2	NAME: D10B-SE-4g-MPG	NINGBO DEGSON ELECTRICAL CO., LTD	
CHKD: CHK 2017.7.1	TITLE: CUSTOMER DRAWING	NINGBO DEGSON ELECTRICAL CO., LTD	
DRFT: Mr.yang 2017/06/28	DRAWING NO: DO NOT SCALE	NINGBO DEGSON ELECTRICAL CO., LTD	
THIRD ANGLE PROJECTION		NINGBO DEGSON ELECTRICAL CO., LTD	
DETACHED LISTS		NINGBO DEGSON ELECTRICAL CO., LTD	
REV. D0-1		NINGBO DEGSON ELECTRICAL CO., LTD	
SHEET 1/1		NINGBO DEGSON ELECTRICAL CO., LTD	
SCALE 1:1		NINGBO DEGSON ELECTRICAL CO., LTD	