

圖號 DRAWING No. :		校訂版次 REVISIONS																	
品名 NAME: Spade	ITEM No. :	<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th style="width: 10%;">版次</th> <th style="width: 50%;">記述 DESCRIPTION</th> <th style="width: 20%;">DATE</th> <th style="width: 20%;">核可</th> </tr> <tr><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td></tr> </table>	版次	記述 DESCRIPTION	DATE	核可													
版次	記述 DESCRIPTION	DATE	核可																

MAXIMUM ELECTRIC CURRENT

A. W. G	12	10
MAX AMP	35	50

NOTE:


1. MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS


2. WIRE RANGE: 12-10 AWG / 4-6 mm²
INSULATED COLOR: YELLOW

3. MATERIAL THICKNESS: t
TOLERANCE: ±0.05



WIRE RANGE AWG/mm ²	產品編號 ITEM NO.	d2 ±0.20	B ±0.20	F ±0.30	L ±1.00	E ±0.60	D ±0.30	d1 ±0.20	t
12-10 AWG 4-6 mm ²		3.7	7.2	7.5	25.2	12.5	6.5	3.4	1.0
		3.7	8.5	7.5	25.2				
	ST-091/Y	4.3	8.5	7.5	25.2				
		4.3	9.5	7.5	25.2				
		5.3	9.5	7.5	25.2				
		6.5	9.5	7.5	25.2				
		6.5	12.0	12.0	31.2				
		8.4	13.5	10.5	30.0				



認可 APPROVALS		第三視角 THIRD VIEW	MATERIAL	單位 UNIT	日期 DATE: 2015. 01. 05
製圖 DRAFT:	TINA		INSULATION: VINYL	m/m	
設計 DESIGN:	KEN		MATERIAL: COPPER	比例 SCALE	
核可 CHECKED:	ANDY		TIN PLATING		