

Flat suction cup (round)

SPF 25 ED-65 G1/8-AG

Part no.:10.01.01.13242

<https://www.schmalz.com/10.01.01.13242>

Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Packaging > Flat Suction
Cups SPF > SPF 25 ED-65 G1/8-AG

Flat suction cup (round) for dynamic handling of cardboard and rigid packaging




Size: 25

Suction cup material: Elastodur

Material hardness: 65 °Sh

Thread G1: G1/8"-M

Design Data



Attribute	Value
dn	4.1 mm
Dmax(S)	28 mm
Ds	26.4 mm
G1	G1/8"-AG
H	17 mm
LG1	7.5 mm
SW1	14 mm
Z (Stroke)	2 mm

Technical Data

Flat suction cup (round)

SPF 25 ED-65 G1/8-AG

Part no.:10.01.01.13242


<https://www.schmalz.com/10.01.01.13242>



Attribute	Value
Suction force (-600mbar)	22.7 N
Pull-off force	27.1 N
Lateral force	17 N
Volume	1.7 cm ³
Curve radius (min) (convex)	30 mm
Hose diameter (empf.) d	4 mm
Size	25
Number of folds	0
Suction cup material	Elastodur
Material hardness [Shore A]	65 Shore A
Weight	7.1 g
Product family	SPF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare Parts



SC 040 G1/8-AG

Part no.10.01.06.02490

Connection element for suction cup "SchmalzConnector"

Connection geometry: 040

Vacuum connection: G1/8"-M

Overall length: 20.2 mm

Fitting length: 6 mm


Nominal diameter dn: 4.1 mm

Flat suction cup (round)

SPF 25 ED-65 G1/8-AG

Part no.:10.01.01.13242

<https://www.schmalz.com/10.01.01.13242>



SPF 25 ED-65 SC040

Part no.10.01.01.12371

Flat suction cup (round) for dynamic handling of cardboard and rigid packaging

Size: 25

Suction cup material: Elastodur

Material hardness: 65 °Sh

Accessories



SIEB 11x1 MS-A2 280 0.28/0.16

Part no.10.07.01.00309

Screen

External diameter D: 11 mm

Length L: 1 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm

Mesh: 0.28 mm

Wire size: 0.16 mm



SU 25

Part no.10.01.01.13584

Cover for suction cup

Size: 25

Clamping range: 25.0 ... 30.0 mm

Temperature resistance: 80 °C