

Bell suction cup (round)

FSGA 43 HT1-60 G1/4-IG

Part no.:10.01.06.00958

<https://www.schmalz.com/10.01.06.00958>



Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows

Suction Cups FSGA (1.5 Folds) > FSGA 43 HT1-60 G1/4-IG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 43

Number of folds: 1.5

Suction cup material:

High temp material HT1


Material hardness: 60 °Sh

Material property: non-marking

Nipple material: Aluminium

Vacuum connection: G1/4"-F

Design Data



Attribute

Value

d2 21.9 mm

Dmax(S) 47.5 mm

dn 4.4 mm

Ds 38 mm

G1 G1/4"-IG

H 42 mm

LG1 12 mm

SW1 17 mm

Z (Stroke) 10 mm

Technical Data

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 1 of 3

Bell suction cup (round)

FSGA 43 HT1-60 G1/4-IG

Part no.:10.01.06.00958


<https://www.schmalz.com/10.01.06.00958>



Attribute	Value
Suction cup material	High temp material HT1
Material hardness [Shore A]	60 Shore A
Size	43
Number of folds	1.5
Connection	G1/4-IG
Curve radius (min) (convex)	60 mm
Volume	9.25 cm ³
Suction force (-600mbar)	22.8 N
Pull-off force	64.5 N
Hose diameter (empf.) d	6 mm
Weight	19 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare Parts



SA-NIP N018 G1/4-IG DN440

Part no.10.01.06.01066

Suction cup connection nipple

Nipple: N 018

Thread G1: G1/4"-F

Overall length: 28.8 mm

Fitting length: 15 mm

Nominal size: 4,40 mm

Material: Aluminium

Spanner size SW2: 5 mm

Bell suction cup (round)

FSGA 43 HT1-60 G1/4-IG

Part no.:10.01.06.00958

<https://www.schmalz.com/10.01.06.00958>



FGA 43 HT1-60 N018

Part no.10.01.06.00874

Bellows suction cup (round) with optimal adaptation to uneven surfaces

Size: 43

Suction cup material:

High temp material HT1

Material hardness: 60 °Sh

Number of folds: 1.5

Material property: imprint-free