

Bell suction cup (round) SPB1 40 ED-65 G1/4-IG

Part no.:10.01.06.03499

<https://www.schmalz.com/10.01.06.03499>



Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Packaging > Bellows

Suction Cups SPB1 (1.5 Folds) > SPB1 40 ED-65 G1/4-IG

Bellows suction cup (round) for very uneven workpieces



Size: 40


Suction cup material: Elastodur

Material hardness: 65 °Sh

Thread G1: G1/4"-F

Number of folds: 1.5

Design Data



Attribute	Value
-----------	-------

d2	26.1 mm
----	---------

dn	6.1 mm
----	--------

Dmax(S)	48 mm
---------	-------

Ds	41.4 mm
----	---------

G1	G1/4"-IG
----	----------

H	47.2 mm
---	---------

LG1	12 mm
-----	-------

SW1	17 mm
-----	-------

Z (Stroke)	16 mm
------------	-------

Technical Data

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 1 of 3

Bell suction cup (round)

SPB1 40 ED-65 G1/4-IG


Part no.:10.01.06.03499

<https://www.schmalz.com/10.01.06.03499>



Attribute	Value
Suction force (-600mbar)	35.9 N
Pull-off force	46.8 N
Lateral force	24.8 N
Volume	18.33 cm ³
Curve radius (min) (convex)	70 mm
Hose diameter (empf.) d	6 mm
Size	40
Number of folds	1.5
Suction cup material	Elastodur
Material hardness [Shore A]	65 Shore A
Weight	22.9 g
Product family	SPB1

Spare Parts



SC 050 G1/4-IG

Part no.10.01.06.02488

Connection element for suction cup "SchmalzConnector"

Connection geometry: 050

Vacuum connection: G1/4"-F

Overall length: 26.5 mm

Fitting length: 17.2 mm

Nominal diameter dn: 6.1 mm

Bell suction cup (round)

SPB1 40 ED-65 G1/4-IG

Part no.:10.01.06.03499

<https://www.schmalz.com/10.01.06.03499>



SPB1 40 ED-65 SC050

Part no.10.01.06.02455

Bellows suction cup (round) with 1.5 corr. for dynamic handling of cardboard and rigid packaging

Size: 40

Suction cup material: Elastodur

Material hardness: 65 °Sh

Number of folds: 1.5

Accessories



SIEB 17.5x0.8 MS-A2 280 0.28/0.16

Part no.10.07.01.00308

Screen

External diameter D: 17.5 mm


Length L: 0.8 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm

Mesh: 0.28 mm

Wire size: 0.16 mm



SPI 33 PA SPB1-40

Part no.10.01.06.03387

Suction cup insert for preventing deformation of sensitive workpieces

Size: 33

Material: Polyamide

Application: SPB1-40