

Bell suction cup (round)

SPB1 25 ED-65 G1/8-AG

Part no.:10.01.06.03494

<https://www.schmalz.com/10.01.06.03494>



Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Packaging > Bellows

Suction Cups SPB1 (1.5 Folds) > SPB1 25 ED-65 G1/8-AG

Bellows suction cup (round) for very uneven workpieces



Size: 25


Suction cup material: Elastodur

Material hardness: 65 °Sh

Thread G1: G1/8"-M

Number of folds: 1.5

Design Data



Attribute	Value
-----------	-------

d2	16.9 mm
----	---------

dn	4.1 mm
----	--------

Dmax(S)	31.3 mm
---------	---------

Ds	26.4 mm
----	---------

G1	G1/8"-AG
----	----------

H	27 mm
---	-------

LG1	7.5 mm
-----	--------

SW1	14 mm
-----	-------

Z (Stroke)	11 mm
------------	-------

Technical Data

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 1 of 3

Bell suction cup (round)

SPB1 25 ED-65 G1/8-AG


Part no.:10.01.06.03494

<https://www.schmalz.com/10.01.06.03494>



Attribute	Value
Suction force (-600mbar)	14.9 N
Pull-off force	23.4 N
Lateral force	13 N
Volume	5.254 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (empf.) d	4 mm
Size	25
Number of folds	1.5
Suction cup material	Elastodur
Material hardness [Shore A]	65 Shore A
Weight	7.1 g
Product family	SPB1

Spare Parts



SC 040 G1/8-AG

Part no.10.01.06.02490

Connection element for suction cup "SchmalzConnector"

Connection geometry: 040

Vacuum connection: G1/8"-M

Overall length: 20.2 mm

Fitting length: 6 mm

Nominal diameter dn: 4.1 mm

Bell suction cup (round)

SPB1 25 ED-65 G1/8-AG

Part no.:10.01.06.03494

<https://www.schmalz.com/10.01.06.03494>



SPB1 25 ED-65 SC040

Part no.10.01.06.02453

Bellows suction cup (round) with 1.5 corr. for dynamic handling of cardboard and rigid packaging

Size: 25

Suction cup material: Elastodur

Material hardness: 65 °Sh

Number of folds: 1.5

Accessories



SIEB 11x1 MS-A2 280 0.28/0.16

Part no.10.07.01.00309

Screen

External diameter D: 11 mm

Length L: 1 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm

Mesh: 0.28 mm

Wire size: 0.16 mm



SPI 22 PA SPB1-25

Part no.10.01.06.03315

Suction cup insert for preventing deformation of sensitive workpieces

Size: 22

Material: Polyamide

Application: SPB1-25