

Mono-Base ISMB 80x80x8


Part no.:10.01.15.00188

<https://www.schmalz.com/10.01.15.00188>



Homepage > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann clamping equipment ISCUP/ISMB/ISQB > ISMB 80x80x8


Mono-Base for Steelplate and Adapterplate



Basic area: 80 x 80 mm mm

Height H: 8 mm

Design Data



Attribute	Value
-----------	-------

B	80 mm
---	-------

d	60 mm
---	-------

H	8 mm
---	------

L	80 mm
---	-------

Technical Data

Attribute	Value
-----------	-------

Weight	0.043 kg
--------	----------


Mono-Base ISMB 80x80x8

Part no.:10.01.15.00188

<https://www.schmalz.com/10.01.15.00188>



Accessories



ISCUP Cup 1 80x80x30

Part no.10.01.15.00003

Suction cup for Innospann

Dimensions (LxW): 80 x 80 mm

Height H: 30 mm



ISCUP Cup 2 80x40x30

Part no.10.01.15.00004

Suction cup for Innospann

Dimensions (LxW): 80 x 40 mm

Height H: 30 mm



ISCUP Cup 3 80x28x30

Part no.10.01.15.00005

Suction cup for Innospann

Dimensions (LxW): 80 x 28 mm

Height H: 30 mm