

Mono-Base ISMB 80x80x42

Part no.:10.01.15.00078

<https://www.schmalz.com/10.01.15.00078>



Homepage > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann clamping equipment ISCUP/ISMB/ISQB > ISMB 80x80x42


Mono-Base for Steelplate and Adapterplate



Basic area: 80 x 80 mm

Height H: 42 mm

Design Data



Attribute	Value
B	80 mm
d	60 mm
H	42 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.19 kg


Mono-Base ISMB 80x80x42

Part no.:10.01.15.00078

<https://www.schmalz.com/10.01.15.00078>



Accessories



ISCUP Cup 1 80x80x30

Part no.10.01.15.00003

Suction cup for Innospann

Dimensions (LxW): 80 x 80 mm

Height H: 30 mm



ISCUP Cup 2 80x40x30

Part no.10.01.15.00004

Suction cup for Innospann

Dimensions (LxW): 80 x 40 mm

Height H: 30 mm



ISCUP Cup 3 80x28x30

Part no.10.01.15.00005

Suction cup for Innospann

Dimensions (LxW): 80 x 28 mm

Height H: 30 mm