

Bell suction cup (round)

SAX 60 ED-85 G3/8-IG

Part no.:10.01.19.00152

<https://www.schmalz.com/10.01.19.00152>



Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal >

Bell-Shaped Suction Cups SAX > SAX 60 ED-85 G3/8-IG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 60


Suction cup material: Elastodur

Material hardness: 85 °Sh

Vacuum connection: G3/8"-F

Nipple material: TPU-GF

Design Data



Attribute	Value
-----------	-------

dn	6.75 mm
----	---------

Dmax(S)	69.7 mm
---------	---------

Ds	61.5 mm
----	---------

G1	G3/8"-IG
----	----------

H	33.4 mm
---	---------

LG1	12 mm
-----	-------

SW1	22 mm
-----	-------

Z (Stroke)	10.9 mm
------------	---------

Technical Data

Bell suction cup (round)

SAX 60 ED-85 G3/8-IG

Part no.:10.01.19.00152

<https://www.schmalz.com/10.01.19.00152>



Attribute	Value
Suction force (-600mbar)	154 N
Lateral force	107 N
Lateral force (oily surface)	155 N
Volume	25.2 cm ³
Curve radius (min) (convex)	30 mm
Size	60
Connection	G3/8"-F
Number of folds	0
Suction cup material	Elastodur
Material hardness [Shore A]	85 Shore A
Weight	29.5 g
Product family	SAX