

Magnetic Grippers

SGM 40 G1/4-IG

Part no.:10.01.17.00163

<https://www.schmalz.com/10.01.17.00163>



Homepage > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic gripper > Magnetic Grippers SGM > SGM 40 G1/4-IG

Magnetic gripper for handling metal sheets with holes



Size: 40


Socket: G1/4"-F

Holding force max friction ring: 100 N

Pressure range (operating pressure):

3.5 ... 6.0 bar

Design Data



Attribute	Value
-----------	-------

B	40.6 mm
---	---------

D	40 mm
---	-------

d	26 mm
---	-------

G1	G1/4"-IG
----	----------

G2	G1/8"-F
----	---------

G4	M4-F
----	------

H	70.2 mm
---	---------

LG1	11 mm
-----	-------

LG2	6 mm
-----	------

LG4	7 mm
-----	------

X1	46 mm
----	-------

Y1	12 mm
----	-------

Magnetic Grippers

SGM 40 G1/4-IG

Part no.:10.01.17.00163

<https://www.schmalz.com/10.01.17.00163>



Technical Data

Attribute	Value
Remaining force	0.3 N
Pressure range (operating pressure)	3.5 ... 6.0 bar
Installation position	Any
Control valve	Bistabil
Operating temperature	5 ... 70 °C
Weight	240 g

Note: Holding force: The value given is a statistical value with no safety factor; based on a plate with a thickness of 2 mm. For system configurations with magnetic grippers SGM, a safety factor of $S = 3$ must be applied

Spare Parts



REIB-RING SGM 40 PU-55

Part no.10.01.17.00137

Friction ring

for: Magnetic gripper

Size: 40

External diameter D: 40 mm

Internal diameter d: 26 mm


Accessories

Magnetic Grippers

SGM 40 G1/4-IG

Part no.:10.01.17.00163

<https://www.schmalz.com/10.01.17.00163>



HTS-A2 SGM 30/40

Part no.10.01.17.00169

Holder system

Cross-beam connection:

Bolt with slot Ø19mm

for: Magnetic gripper

Size: 30/40



HTS-A3 SGM 30/40

Part no.10.01.17.00170


Holder system

Cross-beam connection:

Ball head 28.5 mm

for: Magnetic gripper

Size: 30/40



HTS-A2 D SGM 30/40

Part no.10.01.17.00175

Holder system

Cross-beam connection:

Bolt with slot Ø19mm

Shape: Double block

for: Magnetic gripper

Size: 30/40

Magnetic Grippers

SGM 40 G1/4-IG

Part no.:10.01.17.00163

<https://www.schmalz.com/10.01.17.00163>



HTS-A3 D SGM 30/40

Part no.10.01.17.00176

Holder system

Cross-beam connection:

Ball head 28.5 mm

Shape: Double block

for: Magnetic gripper

Size: 30/40



STV-GE G1/8-AG 6

Part no.10.08.02.00204

Push-in Fitting, straight

Thread G1: G1/8"-M

External hose diameter: 6 mm

Material: Brass

Surface: nickel plated

Ambient temperature: -20 ... 80 °C



STV-W G1/8-AG 6

Part no.10.08.02.00158

Push-in Fitting, swivelling elbow

Thread G1: G1/8"-M

External hose diameter: 6 mm

Material: Brass, nickel-plated

Ambient temperature: -20 ... 80 °C

Magnetic Grippers

SGM 40 G1/4-IG

Part no.:10.01.17.00163

<https://www.schmalz.com/10.01.17.00163>



VSL 6-4 PU

Part no.10.07.09.00002

Hose for vacuum and compressed-air systems

External diameter D: 6 mm

Internal diameter d: 4 mm

Length (max): 500 m

Material: PU

Installation radius (min): 35 mm

Pressure range (operating pressure):

-0.95 ... 10.00 bar

Ambient temperature: -20 ... 90 °C