

Basic ejector SBP 15 G02 SDA

Part no.:10.02.01.00602

<https://www.schmalz.com/10.02.01.00602>




Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > Basic Ejectors SBP > SBP 15 G02 SDA

Basic ejector for universal use



Nozzle size: 1,5 mm
with: Axial silencer
Degree of evacuation: 85 %
Connection: G1/8"(1)-G1/8"(2)
Pressure optimal: 4.5 bar
Suction rate (max): 71 l/min
Air consumption (during evac.):
105 l/min

Design Data



Attribute	Value
-----------	-------

B	15 mm
d	4.2 mm
D	14 mm
G1	G1/8"-IG
G2	G1/8"-F
H	34 mm
H1	42 mm
H2	5.2 mm
H3	14 mm
L	51.5 mm
L1	102 mm
L2	22 mm
L3	10 mm

Basic ejector SBP 15 G02 SDA

Part no.:10.02.01.00602

<https://www.schmalz.com/10.02.01.00602>



Attribute	Value
L4	12.5 mm
LG1	8 mm
LG2	8 mm
SW1	14 mm
SW2	14 mm
X1	20 mm

Technical Data

Attribute	Value
Nozzle diameter	1.5 mm
Degree of evacuation	85 %
Suction rate (max.)	4.3 m³/h
Suction rate (max.)	71 l/min
Air consumption suction	6.3 m³/h
Air consumption suction	105 l/min
Sound level free	72 dB(A)
Sound level suction	65 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure optimal	4.5 bar
Recomm. internal hose diameter compressed air	4 mm
Recomm. internal hose diameter vacuum	6 mm
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	43.5...87.0
Suction rate (max.)	2.507 cfm
Air consumption suction	3.707 cfm

Basic ejector SBP 15 G02 SDA

Part no.:10.02.01.00602

<https://www.schmalz.com/10.02.01.00602>



Attribute	Value
Weight	22 g

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Spare Parts



SD G1/8-AG 14x40

Part no.10.02.01.00540


Silencer for vacuum generators

Thread G1: G1/8"-M

External diameter D: 14 mm

Length L: 40 mm

Accessories



BEF-PL 110x44.5x3 SBP

Part no.10.02.01.00511

Mounting plate

Length L: 110 mm

Width B: 44.5 mm


Height H: 3 mm

for: Basic ejectors SBP

Basic ejector SBP 15 G02 SDA

Part no.:10.02.01.00602

<https://www.schmalz.com/10.02.01.00602>



SET SBP M4-IG

Part no.10.02.01.00769


Mounting set
for: Basic ejectors SBP
Type: M4-IG



VFT G1/4-IG 80

Part no.10.07.01.00119

Vacuum cup filter with transparent housing and
replaceable filter
Connection: G1/4"-F
Shape: Short filter insert
Nominal flow rate: 6.6 m³/h
Filter pore size: 80 µm



VS-V-W-D PNP K 3C-D

Part no.10.06.02.00678

Vacuum/pressure switch in cube shape with display and
digital output signals
Measuring range: -1.0 ... 0.0 bar
Shape: Cube, digital display
Type: Switches to plus
Electrical connection: Cable
Inputs/outputs: 2 digital
Display: 3-color / 2-line

Basic ejector SBP 15 G02 SDA

Part no.:10.02.01.00602

<https://www.schmalz.com/10.02.01.00602>



VS-P10-W-D PNP K 3C-D

Part no.10.06.02.00680

Vacuum/pressure switch in cube shape with display and digital output signals

Measuring range: 0.0 ... 10.0 bar

Shape: Cube, digital display

Type: Switches to plus

Electrical connection: Cable

Inputs/outputs: 2 digital

Display: 3-color / 2-line