

LED STRIP 28LED/M • 24V • 3W • 4000K • IP20 • 400LM • RA80 • 8MM



High quality LED strip for professional use with seven LEDs in one module to achieve luminous efficacy up to 140 lm/W. Two layers of PCB with 3oz copper paths characterized by a lower voltage drop and lower operating temperature. On a base using adhesive tape 3M 300 LSE. LEDs that meet requirements of LM-80 test, guaranteeing small lumen decrease and colour constancy in time.

- 3W /m
- 24V DC
- 140 lm/W LM80 SDCM ≤ 3
- 25.0cm cutting length
- 3oz 8mm FPC
- Ra>80, available over 95
- 75000h L70 lifespan
- 30m reel for IP20, 10m for IP66 / IP68
- Warranty 3 - 5 years

Specification

Parameter	Value
Symbol	SPE-28-NW-24
EAN13	5901289754323
ETIM CLASS	Light ribbon-/hose/-strip
Power	3 W
Voltage	24 V
cutting length	25 cm
Colour of light	White
Model	Tape
Number of nodes per meter	28
Voltage type	DC
Beam angle	120 °
Wskaźnik oddawania barw CRI	>80
With Self-adhesive	yes
Colour temperature	4000 K
Degree of protection	IP20
Suitable for use	
Luminous flux	400 lm
Rated life time L70/B50 at 25 °C	75000 h
Width	8 mm
Height/depth	1.4 mm