

No power supply, battery or maintenance required.

Typical Specifications



Items	Specifications
Power generation	170 μ J (for each operation)
Travel	3.3mm
Operating force	6N $\pm$ 1.5N
Operating life	1,000,000 cycles

Product Line

Poles	Operating	Terminal type	Minimum order unit (pcs.)		Product No.
			Japan	Export	
1	Push	For PC board	320	320	SPGA110100

Packing Specifications

Tray

Number of packages (pcs.)		Export package measurements (mm)
1 case /Japan	1 case /export packing	
320	320	360×270×230

Dimensions

Unit:mm

Style	PC board mounting hole dimensions

Reference for Hand Soldering Condition

Soldering temperature	Soldering time
350 $\pm$ 5 $^{\circ}$ C	3s max.