

BROOKLYN S3 SRC



NYLON MESH/NUBUCK LEATHER SHOES - S3 HRO SRC

Ref. BROOKLYNS3



Product specifications

Upper: Suede split leather (cowhide), S3 water resistant treatment with front rubber reinforcement.
Lining: Polyester non-woven and knitted mesh. Insole: Removable premolded - Polyester on EVA. Outsole: Cemented - Phylon. Outsole: Rubber. Non metallic shoe.

COLOUR

Black-Orange

SIZE

39, 40, 41, 42, 43, 44, 45, 46, 47

Product Use - Risks



Antistatic



Heat



Cutting / Perforation



Slip



Shock



Second work / craftman



Light industry



Services / Logistics

Product's highlights & user's benefits



RUBBER NITRILE OUTSOLE

Good resistance to abrasion and contact heat
(HRO = 300°C for 1 minute)
Optimum adhesion

WELDED SOLE WITH PHYLON MIDSOLE (EVA)

Incomparable comfort and lightness



Quilted collar and tongue

Reduction of pressure points at the lacing



Outsole with protection rubber toe bumper

Reinforced protection of the forefoot



Composite toe cap 200j

Lightweight and less fatigue
Non conductive hot and cold



NON METALLIC

Compatible with security checks (metal detectors)



Anti-perforation composite protective midsole

Increased flexibility at the metatarsal level



Rear support of the reflective upper

Optimal stabilisation of the foot when walking
Increased visibility

Anti-slide on the inside of the shoe

Improved heel hold
Reinforced rear section

EVA outsole preformed and removable

Reinforced ergonomics and comfort in foot movements



COMPOSITE

Certifications and Standards



REGULATION (EU) 2016/425

EN ISO 20344:2011 Personal protective equipment - Test methods for footwear

EN ISO 20345:2011 Personal protective equipment - Safety footwear.

S3 HRO: Additional special requirements

SRC: Slip resistance

References

References	Bar code	COLOUR	SIZE		
BROOKS3NO40	3295249230456	Black-Orange	40	10	-
BROOKS3NO41	3295249230463	Black-Orange	41	10	-
BROOKS3NO42	3295249230470	Black-Orange	42	10	-
BROOKS3NO43	3295249230487	Black-Orange	43	10	-
BROOKS3NO44	3295249230494	Black-Orange	44	10	-
BROOKS3NO45	3295249230500	Black-Orange	45	10	-
BROOKS3NO46	3295249230517	Black-Orange	46	10	-
BROOKS3NO47	3295249230524	Black-Orange	47	10	-
BROOKS3NO39	3295249230425	Black-Orange	39	10	-