

KHE 2860 Quick (600878500) Combination Hammer
(220-240 V / 50 - 60 Hz); Plastic Carry Case; with Metabo Quick change chuck

Order no. 600878500
EAN



Product may differ from Image



- Combination hammer with 3 functions: hammer drilling, drilling and chiselling
- Metabo Quick: quick change between SDS Plus hammer chuck and keyless chuck for drilling in wood and metal
- Perfect ergonomics thanks to the centre of gravity being near the hand and optimised handle contour
- Bottom switch protected against damage and dust
- Vario (V)-Electronics for working at customised speeds to suit various application materials
- Metabo Marathon-motor with dust protection for long service life
- High performance hammer action, precisely mounted in a housing made of aluminium alloy: long-lasting and robust
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- Lockable switch for comfortable working in continuous operation
- Cable-protecting ball joint for optimal freedom of motion when working

Technical data

Characteristics

Max. single blow energy (EPTA)	3.2 J
Maximum impact rate	4400 bpm
Rated input power	880 W
Drill-Ø concrete with hammer drills	28 mm / 1 3/32 "
Drill-Ø masonry with core bits	68 mm / 2 11/16 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	32 mm / 1 1/4 "
No-load speed	0 - 1150 rpm
Revolutions at rated load	870 rpm
Bit retainer	SDS-plus
Collar diameter	50 mm / 1 31/32 "
Weight (without power cable)	3.1 kg / 6.9 lbs
Cable length	4 m / 13 ft

Vibration

Hammer drilling concrete	12.9 m/s ²
Uncertainty of measurement K	2.4 m/s ²
Chiseling	8.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	89 dB(A)
Sound power level (LwA)	99 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Hammer chuck for tools with SDS-plus shank end
 Drilling depth guide
 Plastic carry case
 Keyless chuck for tools with cylindrical shank
 rubber-coated side handle