



Pigtail fiber optic LC/UPC | Multimode | 50/125 | OM2 | 1m

Product code: 54102

Pigtail fiber optic multimode

Connectors: LC/UPC

Standard: OM2

Diameter cable: 0.9 mm

Cable length: 1 m

Technical data

Type connectors	LC/UPC
Type pigtail	Multimode
Standard fiber	OM2
Fiber core diameter	50/125 m
Sheath	LSZH
Diameter cable	0.9 mm
Insertion loss	<0.3 dB
Return loss	35 - 39 dB
Cable length	1 m
Colour	Orange
Additional information	Easy installation and handling on high speed fiber optical transmission networks. LSZH - Outside fireproof cable sheath, which the fire does not emit harmful gases. The product individually tested.
Package	Polybag
Gross weight	0,004 kg
EAN code	5901878541020