



Pigtail fiber optic SC/APC | Singlemode | 9/125 | G652D | 1.5m

Product code: 54110

Pigtail fiber optic singlemode

Connectors: SC/APC

Standard: G652D

Diameter cable: 0.9 mm

Cable length: 1.5 m

Technical data

Type connectors	SC/APC
Type pigtail	Singlemode
Standard fiber	G652D
Fiber core diameter	9/125 m
Sheath	LSZH
Diameter cable	0.9 mm
Insertion loss	<0.3 dB
Return loss	>60 dB
Cable length	1.5 m
Colour	White
Additional information	Easy installation and handling on high speed fiber optical transmission networks. LSZH - Outside fireproof cable sheath, which the fire does not emit harmful gases. The product individually tested.
Package	Polybag
Gross weight	0,008 kg
EAN code	5901878541105