



Pigtail fiber optic ST/UPC | Singlemode | 9/125 | G652D | 3m

Product code: 54124

Pigtail fiber optic singlemode

Connectors: ST/UPC

Standard: G652D

Diameter cable: 0.9 mm

Cable length: 3 m

Technical data

Type connectors	ST/UPC
Type pigtail	Singlemode
Standard fiber	G652D
Fiber core diameter	9/125 m
Sheath	LSZH
Diameter cable	0.9 mm
Insertion loss	<0.3 dB
Return loss	>55 dB
Cable length	3 m
Colour	White
Additional information	Easy installation and handling on high speed fiber optical transmission networks. LSZH - Outside fireproof cable sheath, which the fire does not emit harmful gases. The product individually tested.
Package	Polybag
Gross weight	0,01 kg
EAN code	5901878541242