

ECG28MEDIA-I



Specifications

ETI Code	001101157
Description	ECG28MEDIA-I
Weight	2.5
Level	Multimedia boards
Catalogue Group	ECG flush mounted Multimedia distribution boxes IP30
Mounting type	Flush mounted
Rows	2
Type of door	Perforated metal door, white

Online product page 

Other documentation



Technical data catalogue

Instruction manual

EU declaration

Dimension drawing

Flush mounted distribution board - metal door						
type	Dimensions					Max. allowed power losses when Max. number of devices are installed
	A	B	C	H	W	Pde
ECG14	274 mm	306 mm	87 mm	317 mm	346 mm	31W
ECG28	399 mm	306 mm	87 mm	442 mm	346 mm	40W
ECG42	549 mm	306 mm	87 mm	592 mm	346 mm	50W
ECG56	673 mm	306 mm	87 mm	717 mm	346 mm	60W
ECG70	806 mm	317 mm	87 mm	842 mm	346 mm	60W

