

ECG42



Specifications

ETI Code	001101027
Description	ECG42
Weight	3
Level	Flush-mounted plastic boards IP40 with metal door
Rows	3
Mounting type	Flush mounted
Type of door	Metal door, white
Height (mm)	592
Width (mm)	346
Depth (mm)	88
IP rating	IP40
Catalogue Group	ECG flush mounted compact distribution boxes IP40

Online product page [link](#)

Other documentation



Technical data catalogue
Instruction manual
EU declaration



ETIM international clasification

Mounting method	Flush mounted (plaster)
Colour	White
Width	346mm
Height	592mm
Depth	96mm
RAL-number	
With mounting plate	true
Built-in depth	88mm
Number of rows	3
EMC-version	true
Extension possible	
With transparent cover	
DIN-rail	false
	Closed
Material housing	Plastic
Width in number of modular spacings	14

Type of closure	NULL
Type of door	Metal door, white
Degree of protection (IP)	IP40

Dimension drawing

Flush mounted distribution board - metal door						
type	Dimensions					Max. allowed power losses when Max. number of devices are installed
	A	B	C	H	W	Pde
ECG14	274 mm	306 mm	87 mm	317 mm	346 mm	31W
ECG28	399 mm	306 mm	87 mm	442 mm	346 mm	40W
ECG42	549 mm	306 mm	87 mm	592 mm	346 mm	50W
ECG56	673 mm	306 mm	87 mm	717 mm	346 mm	60W
ECG70	806 mm	317 mm	87 mm	842 mm	346 mm	60W

