

ERP18-4



Specifications

ETI Code	001101214
Description	ERP18-4
Weight	7.708
Level	Flush-mounted plastic boards IP40 with metal door
Rows	4
Mounting type	Flush mounted
Type of door	White door
Height (mm)	715
Width (mm)	451
IP rating	IP40
Catalogue Group	DIDO ERP

Online product page 

Other documentation



Technical data catalogue
EU declaration



ETIM international clasification

Mounting method	Flush mounted (plaster)
Colour	White
Width	451mm
Height	715mm
Depth	120mm
RAL-number	
With mounting plate	
Number of rows	4
Type of cover	
EMC-version	true
Extension possible	
Internal depth	mm
DIN-rail	true
Material housing	Plastic
Width in number of modular spacings	18
Degree of protection (IP), front side	IP40
Type of door	White door
Degree of protection (IP)	IP40
Transparent cover/door	

With lock

Cover model