



PLC Splitter 1x8 | G.657A | Singlemode | 0.9mm

Product code: 54204

Optical splitters allow the division of power between the input optical signal splitter output ports.
Type: 1 x 8 (mini typ)
Standard: G.657A

Technical data

Power handling	300 mW
Operating wavelength	1280 - 1650 nm
Insertion loss max.	< 10.8 dB
Return loss min.	50 (55) dB
Standard	G.657A
Fiber type	Singlemode
Uniformity max.	< 1.0 dB
PDL max.	< 0.2 dB
Directivity min.	55 dB
Diameter cable	0.9 mm
Cable length	1.5 m
Operating temperature	-40 C ~ +85 C
Storage temperatures	-40 C ~ +85 C
Usage	Fiber to The point (FTTX) Fiber to the home (FTTH) Passive optical networks (PON) Local Area Networks (LAN) Cable Television (CATV)
Type	1 x 8
Package	Blister
Gross weight	0,067 kg
EAN code	5901878542041