



## Patchcord fiber optic FC/UPC - LC/UPC | Singlemode | 9/125 | G652D | Simplex | 20m

Product code: 54310

Patchcord fiber optic singlemode  
Connectors: FC/UPC - LC/UPC  
Standard: G652D  
Diameter cable: 3.0 mm  
Cable length: 20 m

### Technical data

|                                  |                                                                                                                                                                                                             |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type connectors                  | FC/UPC - LC/UPC                                                                                                                                                                                             |
| Type patchcord                   | Singlemode                                                                                                                                                                                                  |
| Type of fiber optic transmission | Simplex                                                                                                                                                                                                     |
| Standard fiber                   | G652D                                                                                                                                                                                                       |
| Fiber type                       | 9/125                                                                                                                                                                                                       |
| Diameter of the mode field       | 9 m                                                                                                                                                                                                         |
| Diameter fibers sheath           | 125 m                                                                                                                                                                                                       |
| Sheath                           | LSZH                                                                                                                                                                                                        |
| Diameter cable                   | 3.0 mm                                                                                                                                                                                                      |
| Cable length                     | 20 m                                                                                                                                                                                                        |
| Reinforcing element              | Aramid fiber                                                                                                                                                                                                |
| Additional information           | Easy installation and handling on high speed fiber optical transmission networks.<br>LSZH - Outside fireproof cable sheath, which the fire does not emit harmful gases.<br>The product individually tested. |
| Gross weight                     | 0,136 kg                                                                                                                                                                                                    |
| EAN code                         | 5901878543109                                                                                                                                                                                               |