




Order Code	TCK-098
Inductance	22 μ H $\pm$ 20% (at 1 kHz / 250 mV)
Impedance (DCR)	110 mOhm max.
Rated Current	1.5 A max.
Operating Temperature	-40°C to +125°C




Impedance Curve



Outline Dimensions



PCB PATTERN



Dimensions [mm]

A	7.0 $\pm$ 0.5
B	7.8 $\pm$ 0.5
C	5.0 $\pm$ 0.7
D	2.1 typ.
E	7.5
F	3
G	2