

1 2 3 4 5 6 7 8 9 10 11 12 13 14

A

B

C

D

E

F

G

H

I

J

A

B

C

D

E

F


G

H

I




J

5000±30 mm



P1

Cable Spec.



P2



- Full HD SVGA Monitorkabel
- 15 pol. HD-Stecker > 15 pol. HD-Stecker
- max. Auflösung WUXGA / Full HD 1920 x 1080
- 3x Coax (RGB) + 8 sync Leiter
- mit 2 Ferrit Kernen
- AWG 28/30
- Material:
 - Innenleiter: CCS, BC
 - Isolierungen: PE/PVC
 - Kontakte: vergoldet
 - Geflecht: Aluminium
- RoHS-konform

- Full HD SVGA monitor cable
- 15 pin HD plug > 15 pin HD plug
- max. resolution WUXGA / Full HD 1920 x 1080
- 3x Coax (RGB) + 8 sync wires
- with 2 ferrit cores
- AWG 28/30
- Material:
 - Inner conductor: CCS, BC
 - Insulations: PE/PVC
 - Contacts: gold-plated
 - Braiding: Aluminium
- RoHS compliant

Änderungen

Datum	Name	gez.:	Datum	Name
14.05.2018	tf	gepr.:	12.02.2013	tf
		Norm:		
Änderungen vorbehalten / Subject to change				

Bezeichnung

CAK SVGA XGA
500 15M/15M 5m

Zeichnungs-Nr.:

50490

gobay®

Blatt

von

1 2 3 4 5 6 7 8 9 10 11 12 13 14