



Electric Components > Products > Circular connectors > M23 Signal > M23 Signal housing > M23 Signal cable connector > [M23 Signal cable connector](#)

7.166.500.00S M23 Signal cable connector

Cable diameter	7 – 12 mm
Locking type	Other
Material housing	brass, Die Casting
Material housing surface	Nickel
Material seals/o-rings	NBR
Protection class	IP 67, IP 69 K
Temperature range	-40°C to +125°C
Version	TWILOCK-S

- // Housing without contact inserts
- // Electrical data depend on the contact insert
- // Pluggable with Speedtec
- // [M23 Signal Inserts](#)
- // [M23 Signal Contacts](#)
- // [M23 Signal Accessories](#)
- // You can find further information in the [Technology Center](#)

Additional information

- // [Produktbeschreibungen \(Englisch\)](#)
- // [TWILOCK Product Video](#)

