

BS 18 L BL Q (602327840) Cordless Drill / Screwdriver
18V ; MetaLoc

Order no. 602327840
EAN 4007430337559



Product may differ from Image



- Brushless drill/screwdriver with compact design for universal and demanding applications
- Metabo Quick System: quick change of bit retainer and bits, for flexible working
- Integrated LED work light with night light function for optimal brightness in the work area
- Handy belt hook and bit holder can be fixed either on the right or left side
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

Technical data

Characteristics

Battery voltage	18 V
Maximum torque - soft	25 Nm / 221.3 in-lbs
Maximum torque, hard	60 Nm / 531 in-lbs
Adjustable torque	0.5 - 5 Nm // 4.4 - 44.3 in-lbs
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	32 mm / 1 1/4 "
No-load speed	0 - 550 / 0 - 1850 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 0.51181 "
Weight (including battery pack)	1.2 kg / 2.6 lbs

Vibration

Drilling in metal	2.3 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	72 dB(A)
Sound power level (LwA)	83 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Quick-change chuck
without battery pack, without charger
Belt hook and bit case
MetaLoc case