

## **CC 18 LTX BL (600349840) Cordless Angle Grinders** **18V ; MetaLoc**

Order no. 600349840

EAN 4061792174788



Product may differ from Image



- Very handy tool with maximum working comfort for many applications
- Always the right accessories: large selection of discs to process metal, wood, stone, tiles and plastic.
- Powerfull brushless motor for quick work progress and highest efficiency
- Overload protection: protects the motor from overheating
- Restart protection: prevents unintentional start-up after battery pack change
- Battery packs with capacity display for checking the charge status

## Technical data

### Characteristics

|                                 |                |
|---------------------------------|----------------|
| Battery voltage                 | 18 V           |
| Grinding wheel Ø                | 76 mm / 3 "    |
| Max. cutting depth              | 19 mm / 3/4 "  |
| No-load speed                   | 20000 rpm      |
| Spindle thread                  | M 5            |
| Weight (including battery pack) | 1 kg / 2.2 lbs |

### Vibration

|                              |                      |
|------------------------------|----------------------|
| Surface grinding             | 4.5 m/s <sup>2</sup> |
| Uncertainty of measurement K | 1.5 m/s <sup>2</sup> |
| Grinding with sandpaper      | 3.3 m/s <sup>2</sup> |
| Uncertainty of measurement K | 1.5 m/s <sup>2</sup> |

### Noise emission

|                              |           |
|------------------------------|-----------|
| Sound pressure level         | 77 dB(A)  |
| Sound power level (LwA)      | 88 dB(A)  |
| Uncertainty of measurement K | 1.5 dB(A) |

## Scope of delivery

Clip for cut-off guard  
 Cutting and grinding disc Combinator Inox  
 Allen key  
 MetaLoc case  
 without battery pack, without charger  
 2 Cutting discs Flexiarapid Super Inox  
 2 Cutting discs Flexiarapid Super Universal