

ASE 18 LTX (602269850) Cordless Sabre Saw
18V ; Cardboard box

Order no. 602269850
EAN 4007430187727



Product may differ from Image



- Robust die-cast aluminium gear housing, coated for optimum handling
- Variospeed (V) Electronics for working with customised stroke rates for the materials used
- Saw blade rotatable by 180° for working comfortably overhead
- Metabo Quick for changing saw blades without tools
- Depth guide can be adjusted for ideal utilisation of the saw blade and diverse applications such as plunge cuts
- Wide range of uses thanks to the adapted Metabo saw blade range
- Battery packs with capacity display for checking the charge status
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

Technical data

Characteristics

Battery voltage	18 V
Strokes in idle	0 - 2700 rpm
Saw blade stroke	30 mm / 1 3/16 "
Weight (including battery pack)	3.6 kg / 7.9 lbs kg

Vibration

Sawing chipboards	16 m/s ²
Sawing wooden beam	16 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	84 dB(A)
Sound power level (LwA)	95 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Hexagonal wrench
without battery pack, without charger