

STAB 18 LTX 100 (601003840) Cordless Jigsaw
18V ; MetaLoc

Order no. 601003840
EAN 4007430324573



Product may differ from Image



- Precise and material-matched sawing due to the variable stroke rate, pendulum stroke and low-lying saw blade guidance with spring support
- Metabo "Quick" for changing saw blades without tools and with automatic ejection
- Top handle with non-slip soft-grip surface
- Selectable shaving blower function ensures free view of cutting line
- Battery packs with capacity display for checking the charge status
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

Technical data

Characteristics

Battery voltage	18 V
Cutting depth wood	100 mm / 4 "
Cutting depth NF metal	25 mm / 1 "
Cutting depth sheet steel	10 mm / 3/8 "
Swivel range from / to:	- 45 / + 45 °
Pendulum stroke levels	4
Strokes in idle	0 - 2800 rpm
Weight (including battery pack)	2.6 kg / 5.8 lbs

Vibration

Sawing wood	9.8 m/s ²
Sawing metal	6.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	84 dB(A)
Sound power level (LwA)	95 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Extraction nozzle
 Hexagonal wrench
 MetaLoc case
 without battery pack, without charger
 Protective glass
 Chip guard plate