

BS 18 LT BL (602325840) Cordless Drill / Screwdriver
18V ; MetaLoc

Order no. 602325840
EAN 4007430297747



Product may differ from Image



- Brushless drill/screwdriver with compact design for universal and demanding applications
- Unique Metabo brushless motor for quick work progress and highest efficiency when drilling and screwdriving
- Integrated working light to illuminate the contact area
- Handy belt hook and bit holder can be fixed either on the right or left side
- Battery packs with capacity display for checking the charge status
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

Technical data

Characteristics

Battery voltage	18 V
Maximum torque - soft	34 Nm / 301 in-lbs
Maximum torque, hard	60 Nm / 531 in-lbs
Adjustable torque	0.7 - 8 Nm // 6 - 71 in-lbs
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	38 mm / 1 1/2 "
No-load speed	0 - 600 / 0 - 2100 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight (including battery pack)	1.5 kg / 3.3 lbs

Vibration

Drilling in metal	3.2 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	76 dB(A)
Sound power level (LwA)	87 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Keyless chuck
without battery pack, without charger
Belt hook and bit case
MetaLoc case