

BS 18 LTX Impuls (602191840) Cordless Drill / Screwdriver
18V ; MetaLoc

Order no. 602191840
EAN 4007430286949



Product may differ from Image



- Selectable "impuls" mode for removal of stubborn screws and for spot-drilling on smooth surfaces
- Powerful Metabo 4-pole motor for fast drilling and screwdriving
- Overload protection: protects the motor from overheating
- Spindle with hexagonal recess for screwdriver bits for working without chuck
- Collar (Ø 43 mm) for versatile use
- Integrated working light to illuminate the contact area
- Robust die cast aluminium gear housing for optimum heat dissipation and long service life
- Handy belt hook, can be fixed either on the right or left side
- Battery packs with capacity display for checking the charge status
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

Technical data

Characteristics

Battery voltage	18 V
Maximum torque - soft	55 Nm / 487 in-lbs
Pulse torque	60 Nm / 531 in-lbs
Maximum torque, hard	110 Nm / 974 in-lbs
Adjustable torque	1.5 - 24 Nm // 13 - 221 in-lbs
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	65 mm / 2 1/2 "
No-load speed	0 - 500 / 0 - 1700 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight (including battery pack)	2 kg / 4.4 lbs

Vibration

Drilling in metal	2.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²
Screwdriving without impact	2.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	80 dB(A)
Sound power level (LwA)	91 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Futuro Plus keyless chuck with metal sleeve
 MetaLoc case
 without battery pack, without charger
 Side handle
 Belt hook