

SSD 18 LTX 200 BL (602396840) Cordless Impact Driver
18V ; MetaLoc

Order no. 602396840
EAN 4007430330147



Product may differ from Image



- Compact cordless impact driver with 1/4" hexagon socket and 200 Nm
- Unique Metabo brushless motor for quick work progress and highest efficiency for any application
- Automatic Power Shift (APS) supports working with self-tapping screws: automatic torque reduction after drilling to prevent overtightening.
- Twelve speed/torque levels for a wide range of applications
- Integrated work light for illumination of the work area
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Handy belt hook, can be fixed either on the right or left side
- Battery packs with capacity display for checking the charge status
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

Technical data

Characteristics

Battery voltage	18 V
Max. screw size	M16
Max. no-load speed	2900 rpm
Maximum impact rate	4000 bpm
Maximum torque	200 Nm / 150 ft. lbs
Speed/torque levels	12
Bit retainer	Hexagon recess 1/4" (6.35 mm)
Weight (including battery pack)	1.3 kg / 2.9 lbs

Vibration

Impact screwdriving	9 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	94 dB(A)
Sound power level (LwA)	105 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Belt Hook
MetaLoc case
without battery pack, without charger