

HO 18 LTX 20-82 (602082840) Cordless planer
18V ; MetaLoc

Order no. 602082840
EAN 4007430325075



Product may differ from Image



- Light, compact cordless planer for planing, rebating and chamfering
- Adjustable planer depth and notch depth
- Aluminium die cast and milled cut planer base with V-groove for easy chamfering
- Parallel guide / rip fence for precise guiding of the planer
- Grip area with non-slip soft-grip surface
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Angled chip ejection adapter for controlled ejection of the wood shavings
- Easy to empty textile dust bag for working without extraction facilities
- Strap on the planer base for stopping the machine and to protect the work piece
- Easy blade change of the robust reversible carbide planer blades
- Soft start and overload protection for long service life of motor and drive

Technical data

Characteristics

Battery voltage	18 V
Planing width	82 mm
Adjustable planing depth	0 - 2 mm
Maximum notch depth	9 mm
No-load speed	16000 rpm
Length of planer base	295 mm
Weight (including battery pack)	3.5 kg / 8 g

Vibration

Planing soft wood	1.6 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	90 dB(A)
Sound power level (LwA)	101 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Reversible carbide planer blades
Chip ejection adapter
Textile dust bags
MetaLoc case
without battery pack, without charger
Parallel Guide / Rip Fence
Depth gauge