

SSW 18 LTX 400 BL (602205840) Cordless Impact Wrench
18V ; MetaLoc

Order no. 602205840
EAN 4007430287236



Product may differ from Image



- Unique Metabo brushless motor for quick work progress and highest efficiency for any application
- Overload protection: protects the motor from overheating
- High torque accompanied by an exceptionally compact design
- High torque machine with low kick-back torque
- Twelve speed/torque levels for a wide range of applications
- Integrated work light for illumination of the work area
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Handy belt hook, can be fixed either on the right or left side
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

Technical data**Characteristics**

Battery voltage	18 V
Max. screw size	M20
Max. no-load speed	0 - 2150 rpm
Maximum impact rate	4250 bpm
Maximum torque	400 Nm / 295 ft. lbs
Max. loosening torque	620 Nm / 420 ft. lbs
Speed/torque levels	12
Bit retainer	Male square 1/2" (12.70 mm)

Vibration

Impact screwdriving	12 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	100 dB(A)
Sound power level (LwA)	111 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Belt Hook
MetaLoc case
without battery pack, without charger