

MKS 18 LTX 58 (600771840) Cordless Metal Cutting Circular Saw
18V ; MetaLoc

Order no. 600771840
EAN 4061792000544



Product may differ from Image



- Powerful cordless metal cutting circular saw with chip collection box for cold sawing of metals. Compatible with guide rails.
- Fast and precise cutting of tubes, profiles, channels, metal grids and sheets, free from sparks and burrs.
- With chip collection box for a clean working environment
- Robust saw with guard made from die-cast aluminium and stainless steel base plate
- Lower weight and compact, ergonomic design
- Viewing window in the guard for precise cutting guidance
- Cutting depth control, steplessly adjustable and without tools according to mm and inch scale
- Comfortable saw blade change with spindle lock
- Fast brake for highest safety with quick saw blade stop (< 1 sek)
- Precise straight cuts of metal grids, steel and profile sheets thanks to guide rail (accessory)
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

Technical data

Characteristics

Battery voltage	18 V
Adjustable cutting depth	0 - 58 mm // 0 - 2.28 "
Maximum cutting depth at 90°	58 mm / 2.28 "
Saw blade Ø x bore	165 x 20 mm / 6 1/2 x 5/8 "
Max. cutting speed	31 m/s / 102 ft/min
Weight (including battery pack)	3.7 kg / 8.3 lbs

Vibration

Sawing chipboards	2.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	97 dB(A)
Sound power level (LwA)	108 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Carbide circular saw blade for metal (40 teeth)
 Guide rail adapter
 MetaLoc case
 without battery pack, without charger
 Parallel guide / rip fence
 Hexagonal wrench
 Hexagonal wrench